

**Press Release  
No. 076a/2018**

## **Generation G 7000 dishwashers at a glance\***

<b>Types</b>	Freestanding, built-under, integrated and fully integrated dishwashers; straight or slanted fascia
<b>Technical features</b>	Spray arms controlled separately; EcoPower technology with new water circuit and heat exchanger; sensor-controlled water softener
<b>Dispensing</b>	Automatic AutoDos dispenser system with integrated PowerDisk for 20 cycles**; manual dispensing alternatively possible using tablets and powder
<b>Energy</b>	Up to 'A+++ minus 10%'
<b>Water consumption</b>	from 6 l***
<b>Drying</b>	Sensor-controlled condensation drying, Door opens automatically at end of programme (AutoOpen)
<b>Internal features</b>	FlexLine basket design and 3D MultiFlex drawer, with new adjustment options for a secure hold and flexible use, M Touch on fully integrated models
<b>Convenience features</b>	Interior LED lighting (BrilliantLight), AutoStart****, handleless door opening system (Knock2open), automatic load recognition
<b>Networking</b>	via WiFi
<b>Sales start</b>	November 2018

\* Features depend on model

\*\* In 'Normal 60°C' programme

\*\*\* In 'Automatic' programme

\*\*\*\* to be launched in the second quarter of 2019

**Free for  
editorial use**

**Please submit  
copies to**  
Miele & Cie. KG  
Public Relations

**Postal address**  
P.O.B.  
33325 Gütersloh  
Germany

**Phone**  
+49 5241 89-1953  
**Fax**  
+49 5241 89-1950

[www.miele.de](http://www.miele.de)  
[presse@miele.de](mailto:presse@miele.de)