

Press Release
No. 5a/2019

Brief DGC 7860/65 portrait, flagship 60 cm combi steam oven

Design

Available in the PureLine design line with metal handle and stainless-steel trim; in VitroLine design with a handle in the same colour as the glass front, hence in graphite grey, brilliant white or obsidian black; available as an alternative model with a handleless ArtLine design as the DGC 7860 X in all three colours:

Models DGC 7865 (X) refer to plumbed-in models (DirectWater Plus)

Operating data

24, including various operating modes for combi cooking and classic oven functions; over 100 (in part country-specific) automatic programmes; 20 own programmes can be stored.

User convenience

Mix & Match function for the preparation of plated meals in a single process; with MotionReact, the appliance provides a context-sensitive response to persons approaching the appliance, for example by switching on automatically; wireless food probe for roasting to a core temperature; motorised fascia panel; intuitive M Touch display with search function for automatic programmes; connectivity-ready with numerous further convenience features (WiFi on board); various machine care functions

Further technical details

68 l oven volume with four rack levels; temperature controls between 30° and 225°C; BrilliantLight oven lighting

Accessories

Universal baking sheet and roasting rack with PerfectClean finish; FlexiClip fully telescopic runners; two perforated stainless-steel containers; one unperforated stainless-steel container; cookery book (country-dependent)

Media contact:

Michael Prempert

Phone: +49 5241 89-1957

Email: michael.prempert@miele.com

Text and photo download: www.miele-presse.de

Free for
editorial use

Please submit
copies to
Miele & Cie. KG
Public Relations

Postal address
P.O.B.
33325 Gütersloh
Germany

Phone
+49 5241 89-1953
Fax
+49 5241 89-1950

www.miele.de
presse@miele.de