

Press release  
No. 063/2024

## Miele dishwashers for respiratory equipment at fire stations – with capacities to meet every need

- ▶ Cleaning and disinfection devices in various sizes
- ▶ With inserts for compressed air cylinders and carrying racks

**Gütersloh/Fulda, May 15, 2024. – After each call-out, respiratory equipment must be hygienically reprocessed. Depending on the requirements and available space at the fire station, Miele offers suitable solutions for this application. Compressed air cylinders and their carrying racks can also be cleaned at the same time.**

With a width of only 65 cm, the two PLW 7111 Safety appliances are an ideal solution when space is limited. They are connectivity-enabled, can be operated via the Miele MOVE Internet portal and offer an enlarged chamber. Furthermore, intelligent technology adjusts circulation pump capacity, guaranteeing speed during the main wash and saving water in the rinse cycle. Both models reprocess 16 masks safely and efficiently, and one is available with integrated drying. A new feature in this series is the cleaning of two compressed air cylinders or two carrying frames.

The large-capacity washers from the PLW 86 Safety model series can also be used for reprocessing fire-fighters' respiratory equipment. For example, 24 breathing masks can be used to clean up to two levels. These appliances also offer space for eight small or four large compressed air cylinders. Alternatively, one rinsing cycle prepares four carrying racks.

The large-capacity washers are optionally available with drying and as single- or double-door versions. The latter, when installed in a diaphragm wall, enables the segregation of the clean and dirty operations in a respiratory apparatus workshop, preventing the spread of germs and enabling maximum hygiene safety.

### Media contact

Anke Schläger

Phone: +49 5241 89-1949

Email: [anke.schlaeger@miele.com](mailto:anke.schlaeger@miele.com)

**Company profile:** Miele is recognised as the world's leading supplier of Premium domestic appliances, with an inspiring portfolio for the kitchen, laundry and floor care in the increasingly networked home. The company also offers machines, systems and services for use in hotels, offices, care and medical technology. Since its foundation in 1899, Miele has lived up to its brand promise of "Immer Besser" in terms of quality, innovation, performance and timeless elegance. With its durable and energy-saving appliances, Miele helps its customers to make their everyday lives as sustainable as possible. The company is still owned by the two founding families Miele and Zinkann and has 15 production plants, eight of which are in Germany. Around 22,700 people work for Miele worldwide and the company's most recent turnover was around 5 billion Euro. The company has its headquarters in Gütersloh in Westphalia.

## There are two photographs with this text






**Photo 1:** Plenty of space for cleaning and disinfecting respiratory equipment: a large-capacity washer from the PLW 86 Safety series, in which four large compressed air cylinders can be processed. Models in this series are available with drying and in one or two-door versions. (Photo: Miele)



**Photo 2:** A space-saving solution when there is a high demand for cleaned respirators in a small space: a Miele PLW 7111 Safety washer-dryer with a width of only 65 centimetres. It can also be used to safely and efficiently reprocess compressed air cylinders and carrying equipment. (Photo: Miele)

Text and photo download: [www.miele-press.com](http://www.miele-press.com)

Follow us on:

-  @Miele
-  @Miele\_com
-  Miele | Miele Professional

Further information on this topic is available to users on [www.miele-professional.com](http://www.miele-professional.com)