

Press release  
No. 097a/2024

## The new Guard series at a glance

### Guard S1

<b>Construction type</b>	Cylinder vacuum cleaner with vacuum cleaner bag
<b>Positioning</b>	Entry-level class
<b>Power rating</b>	890 watts
<b>Weight</b>	5.6 kg (incl. accessories)
<b>Vacuum cleaner bag</b>	Miele HyClean Pure TU – 3.5 litre volume; 99.99% filtration in conjunction with Miele AirClean filter; consists of 80% recycled material  Secure latching of the bag to the vacuum cleaner device with an audible click for optimum Hygiene plus and to contactor the vacuum cleaner (ComfortFit)
<b>Operating radius</b>	10 metres
<b>Operation</b>	Rotary control
<b>Power levels</b>	Four (curtains/textiles, upholstered furniture, carpets, hard floors)
<b>Accessories</b>	Dusting brush, crevice nozzle and upholstery nozzle
<b>Networking</b>	Registration possible in the Miele app (shows suitable accessories, warranty status and operating instructions)
<b>Colours</b>	Brilliant white, Obsidian black, Sunset yellow, Terra red
<b>Price</b>	from 189 EUR
<b>Availability</b>	from January 2025

Free to  
editorial  
Usage

Please send supporting documents  
Miele & Cie. KGP.O. Box  
Press and33325 Gütersloh  
Public Relations

toPostal addressPhone  
05241 89-1953  
Fax  
05241 89-1950

www.miele.de  
89-1953presse@miele.de

## Guard M1

<b>Construction type</b>	Cylinder vacuum cleaner with vacuum cleaner bag
<b>Positioning</b>	Middle class
<b>Power rating</b>	550 watts, 700 watts or 890 watts (depending on the model)
<b>Weight</b>	6.6 kg (incl. accessories)
<b>Vacuum cleaner bag</b>	<p>Miele HyClean Pure CO - 3.5 litre volume; 99.99% filtration in conjunction with Miele AirClean filter; consists of 80% recycled material</p> <p>Secure latching of the bag to the vacuum cleaner's retaining plate with an audible click for optimum Hygiene plus and to contactor the vacuum cleaner (ComfortFit)</p>
<b>Operating radius</b>	11 metres
<b>Operation</b>	Mode button
<b>Power levels</b>	Four (curtains/textiles, upholstered furniture, carpets, hard floors)
<b>Accessories</b>	Dusting brush, crevice nozzle and upholstery nozzle (integrated in the appliance)
<b>Networking</b>	Registration possible in the Miele app (shows suitable accessories, warranty status and operating instructions)
<b>Colours</b>	Brilliant white, Casa grey, Nordic blue, Obsidian black, Sunset yellow
<b>Price</b>	from 259 EUR
<b>Availability</b>	from January 2025

## Guard L1

<b>Construction type</b>	Cylinder vacuum cleaner with vacuum cleaner bag
<b>Positioning</b>	Premium class
<b>Power rating</b>	550 watts, 700 watts, 890 watts (depending on the model)
<b>Weight</b>	6.7 kg (incl. accessories)
<b>Vacuum cleaner bag</b>	Miele HyClean Pure TU - 3.5 litre volume; 99.99% filtration in conjunction with Miele AirClean filter; consists of 80% recycled material  Secure latching of the bag to the vacuum cleaner's retaining plate with an audible click for optimum Hygiene plus and to contactor the vacuum cleaner (ComfortFit)
<b>Operating radius</b>	12 metres
<b>Control panel</b>	Large control element with LED display or high-end LCD-display (L1 Comfort)
<b>Power levels</b>	Four (curtains/textiles, upholstered furniture, carpets, hard floors) or five incl. automatic mode (L1 Comfort)
<b>Accessories</b>	Dusting brush, 2 in 1 upholstery and crevice nozzle
<b>Networking</b>	Registration in the Miele app possible (shows suitable accessories, warranty status and operating instructions) or active networking with notification when vacuum cleaner bags or filters need to be changed (L1 Comfort)
<b>Colours</b>	Brilliant white, Casa grey, Nordic blue, Obsidian black, Terra red, Titanium pearl finish
<b>Price</b>	from 299 EUR
<b>Availability</b>	from January 2025